

Полярископ настольного типа PSV-202

Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)34-54-704
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +7(727) 34-54-704

Беларусь +(375) 257-127-88

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: pcs@nt-rt.ru || сайт: <https://ptc.nt-rt.ru/>

ПОЛЯРИСКОП НАСТОЛЬНОГО ТИПА

Поляризованный свет используется для наблюдения и анализа внутреннего напряжения прозрачных стеклянных и пластиковых изделий. Этот метод, часто называемый фотоупругостью, включает пропускание поляризованного света через прозрачный образец и анализ полученных световых рисунков для обнаружения распределения напряжений внутри материала. Это устройство является важным инструментом для отраслей, где целостность материала стеклянных и пластиковых компонентов имеет решающее значение, например, в автомобильной, аэрокосмической и бытовой электронике. Его способность предоставлять подробные сведения о напряжении материала делает его бесценным для поддержания высоких стандартов производства.



Характеристики полярископа настольного типа

- **Своевременное измерение:** уровень напряжения можно измерять в режиме реального времени во время производства, что позволяет немедленно принимать корректирующие меры.
- **Улучшение качества:** за счет выявления и устранения внутренних напряжений повышается общее качество и производительность продукции.
- **Универсальное применение:** идеально подходит для проверки таких материалов, как стекло, пластик, хрусталь и многие другие.
- **Превосходная производительность:** использует импортные оптические компоненты для отображения четких изображений напряжений.

Технические характеристики

Модель №	PSV-202
Замедление двухволновой пластины	560 нм
Поляризатор	200мм*200мм
Анализатор	Диаметр 100мм
Измерение высоты	236мм
Общий размер	310*285*350мм
Напряжение	24 В постоянного тока (в комплекте с адаптером переменного/постоянного тока)
Источник света	Белый светодиодный модуль
Вес нетто	Около 8 кг

BENCH TYPE POLARISCOPE

Polarized light is adopted to observe and analyze the internal stress of transparent glass and plastic products. This method often referred to as photoelasticity, involves passing polarized light through a transparent sample and analyzing the resulting light patterns to detect stress distributions within the material. This device is an essential tool for industries where material integrity of glass and plastic components is critical, such as in automotive, aerospace, and consumer electronics manufacturing. Its ability to provide detailed insights into material stress makes it invaluable for maintaining high-quality production standards.



Features of Bench Type Polariscope

- **Timely Measurement:** Stress can be measured in real-time during production, enabling immediate corrective actions.
- **Improved Quality:** By identifying and mitigating internal stresses, the overall product quality and performance are enhanced.
- **Versatile Applications:** Ideal for inspecting materials such as glass, plastic, crystal, and many others.
- **Premium Performance:** Utilizes imported optical components to display clear stress images.

Specifications

Model No.	PSV-202
Retardation of full-wave plate	560nm
Polarizer	200mm*200mm
Analyzer	Diameter 100mm
Measuring height	236mm
Overall size	310*285*350mm
Voltage	24VDC (supplied with an AC/DC adaptor)
Light source	White LED module
Net weight	About 8KG

По вопросам продаж и поддержки обращайтесь:

Алматы (727)34-54-704
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижегород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +7(727) 34-54-704

Беларусь +(375) 257-127-88

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: pcs@nt-rt.ru || сайт: <https://ptc.nt-rt.ru/>